



# iQ 10 Charging Station<sup>™</sup> Specifications









### **USB Charging**

Equipped with two intelligent USB charging hubs so you can charge up to 10 iPad or other Tablet devices simultaneously. Each port can output up to 2.4 amps of power.<sup>1</sup>

## Power

Input 110~240 VAC Output: 10 x 5V/2.4A

# Baskets by PC Locs (green and blue)

Internal slot dimensions mm: 294.9(H) x 219(L) x 24.5(W) inches: 11.61(H) x 8.62(L) x 0.96(W) External basket dimensions mm: 357.9(H) x 231(L) x 179(W) inches: 14.09(H) x 9.09(L) x 7.05(W)

# Warranty<sup>2</sup>

Lifetime on chassis One year on electrical

# Color

Ripple finish powder coat: White core with charcoal doors and lid

### Construction

Welded steel for strength and durability

#### **External dimensions**

mm: 320(L) x 403(W) x 406(H) inches: 12.6(L) x 15.87(W) x 15.97(H) weight: 13.8 kg | 30.4 lbs

# Certifications

CE (Europe )
SAA (Australia)
UL Compliant (USA and Canada)
KCC (Korea) - pending
SIRIM (Malaysia) - pending
SPRING (Singapore) -pending

28 IAN 15



# DOES YOUR DEVICE FIT IN OUR 5 SLOT BASKETS? CHECK IT HERE. To ensure accurate measurements, please print to scale and on an A3 page (portrait). 24.5 mm STEP 1 – Check the device thickness Check the thickness of your device here. If the device thickness fits within the boundaries of this shape, you're almost there. Go to STEP 2. pclocs STEP 2 – Check the device dimensions 294.9 mm Place your device here. If the device fits within the boundaries of this shape, proceed to STEP 3. STEP 3 – Check device charging point Ensure that the charging point is above the dashed line. If it does, then you're good to go. www.pclocs.com.au PLEASE NOTE: It is your responsibility to ensure you measure your device correctly. If you are planning to use a case with your device, ensure you have it on whilst checking the compatibility. If the device is too thick with the cases installed, but fits with STEP 2 and 3, there is one more option, and that is to remove the moulded device divider from the top of the basket. For details about this option, please contact us for more details.

219 mm